



### Main

Range of product	ConneXium
Product or component type	Ethernet TCP/IP unmanaged switch
Concept	Transparent Ready
Communication port protocol	Ethernet TCP/IP
Port Ethernet	10BASE-T/100BASE-TX - 3 port(s) copper cable
Maximum number of switches in cascade	Unlimited

### Complementary

Integrated connection type	Shielded RJ45 copper cable
Transmission support medium	Twisted shielded pairs cable CAT 5E for copper cable
Ethernet service	Automatic negotiation of 10/100 Mbit/s and duplex mode Auto MDI/MDX Automatic change of polarity Storage and re-routing of received data
[Us] rated supply voltage	24 V
Supply voltage limits	9.6...32 V DC SELV
Power consumption in W	2.2 W
Electrical connection	Removable connector 3 ways power supply
Marking	CE
Local signalling	1 LED power supply 1 LED per channel copper port activity 1 LED per channel 10 or 100 Mbit/s data rate
Ethernet cabling system	TF switches
Width	25 mm
Height	114 mm
Depth	79 mm
Product weight	0.113 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

## Environment

Ambient air temperature for operation	0...60 °C
Relative humidity	> 0...95 % without condensation
IP degree of protection	IP30
Standards	CSA C22.2 No 142 CUL 508
Product certifications	CE

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0744 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">End of Life Information</a>
Product end of life instructions	Available

## Contractual warranty

Warranty period	18 months
-----------------	-----------

---

Power Wiring

---

