

SEK-18 SV MA LP STR45 14P PL3 BLACK



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 18 514 7322 001 |
| Specification | SEK-18 SV MA LP STR45 14P PL3 BLACK |
| HARTING eCatalogue | https://harting.com/09185147322001 |

Identification

| | |
|----------------------------|-----------------|
| Category | Connectors |
| Series | SEK Low-profile |
| Element | Male connector |
| Description of the contact | Straight |

Version

| | |
|--------------------|----------------------------|
| Termination method | Wave soldering termination |
| Connection type | PCB to cable PCB to PCB |
| Number of contacts | 14 |
| Termination length | 4.5 mm |

Technical characteristics

| | |
|------------------------------------|---------------------------|
| Contact rows | 2 |
| Contact spacing (termination side) | 2.54 mm |
| Rated current | 1 A |
| Insulation resistance | $>10^9 \Omega$ |
| Contact resistance | $\leq 20 \text{ m}\Omega$ |
| Limiting temperature | -55 ... +125 °C |
| Insertion force | $\leq 42 \text{ N}$ |
| Withdrawal force | $\leq 42 \text{ N}$ |
| Performance level | 3 acc. to IEC 60603-13 |
| Mating cycles | ≥ 50 |



Pushing Performance
Since 1945

Technical characteristics

| | |
|---------------------------|-------------------------------|
| Test voltage $U_{r.m.s.}$ | 1 kV |
| Isolation group | IIIa ($175 \leq CTI < 400$) |

Material properties

| | |
|---|--|
| Material (insert) | Thermoplastic resin (PBT) |
| Colour (insert) | Black |
| Material (contacts) | Copper alloy |
| Surface (contacts) | Noble metal over Ni Mating side Sn over Ni Termination side |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |

Specifications and approvals

| | |
|------------------------|--|
| Specifications | IEC 60603-13 |
| UL / CSA | UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079 |
| Railway classification | F3/I3 |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 100 |
| Net weight | 2.96 g |
| Country of origin | Romania |
| European customs tariff number | 85366990 |
| GTIN | 5713140214583 |
| eCl@ss | 27460201 PCB connector (board connector) |
| ETIM | EC002637 |
| UNSPSC 24.0 | 39121415 |



Pushing Performance
Since 1945

Cross section of solder termination

