

CK2,5-ED-0,5ST CUNI - Crimp contact



1585744

<https://www.phoenixcontact.com/gb/products/1585744>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper-nickel (constants), connection cross section: 0.5 mm² ... 0.5 mm², AWG 20

Commercial data

Item number	1585744
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	AF7AID
Product key	AF7AID
Catalog page	Page 668 (C-2-2019)
GTIN	4046356308243
Weight per piece (including packing)	1.4 g
Weight per piece (excluding packing)	1.3 g
Customs tariff number	85366990
Country of origin	DE

CK2,5-ED-0,5ST CUNI - Crimp contact



1585744

<https://www.phoenixcontact.com/gb/products/1585744>

Technical data

Notes

General	For HC-M-06, HC-M-HV, HC-M-08, HC-A, HC-BB, HC-B and HC-HV contact inserts, the quality of a crimp connection is determined by the DIN EN 60 352-2
---------	--

Product properties

Product type	Thermal contact
Series	HC-M-06; HC-M-HV; HC-M-08; HC-A; HC-BB; HC-B; HC-HV
Type	Individual male contact
Contact material type	turned


Electrical properties

Rated current	16 A
---------------	------

Connection data

Connection method	Crimp connection
-------------------	------------------

Dimensions

Dimensional drawing	
Width	4.5 mm
Height	4.5 mm
Depth	25 mm

Mechanical characteristics

Contact diameter	2.5 mm
------------------	--------

Material specifications

Contact material	Copper-nickel (constants)
------------------	---------------------------

Cable/line

Stripping length of the individual wire	7.5 mm (9.5 mm at HC-M-HV...)
---	-------------------------------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CK2,5-ED-0,5ST CUNI - Crimp contact



1585744

<https://www.phoenixcontact.com/gb/products/1585744>

Mounting

Assembly note

The quality of a crimp connection is determined by DIN EN 60352-2.


CK2,5-ED-0,5ST CUNI - Crimp contact

1585744

<https://www.phoenixcontact.com/gb/products/1585744>



Drawings



Dimensional drawing

CK2,5-ED-0,5ST CUNI - Crimp contact



1585744

<https://www.phoenixcontact.com/gb/products/1585744>

Classifications

ECLASS

ECLASS-13.0	27440204
-------------	----------

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CK2,5-ED-0,5ST CUNI - Crimp contact



1585744

<https://www.phoenixcontact.com/gb/products/1585744>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk