

**16000btu
Portable Air Conditioner**

Instant cooling and heating



We present the **NEW Koolbreeze Climateasy 16.**

Designed specifically to meet the needs of customers with larger rooms or heavy duty applications, this innovation from **Koolbreeze** incorporates a new energy efficient compressor and a tough body to ensure long life. This portable air conditioner is designed for larger rooms and offices where you require cooling or heating all year round. It can make your lounge or office cool and comfortable and thanks to its quiet operation, it won't disturb your train of thought.

This Portable Air Conditioner packs 16000btu of cooling (and 14500btu heating) power. This model is an air conditioner, heater, dehumidifier and fan. It is an energy efficient multi-season unit utilizing heat pump technology to extract heat from the air while consuming less energy than other portable units .

Our evaporative technology uses any collected moisture to cool the unit before it is eliminated through the exhaust ducts leaving no water bucket to empty.

**Multi-season air conditioner and heater in one
super compact unit**

SPECIFICATION

16000 BTU (4.7 Kw) Cooling

- 14500 BTU (4.2Kw) Heating
- 24-hour programmable on and off timer
- 43 Litre per day evaporative dehumidifier
- Adjustable thermostat down to 16C
- 3 speed fan with oscillating louvres
- Easy rolling casters for portability
- Cooling input 1880 W
- Heating input 1800W
- Air Circulation 500 Cu/m Hr
- Noise ; Less than 65Db Sound Power
- Size 410x440x865mm
- Weight 34Kg net/ 36Kg gross
- Extra long hose 2M x 147mm
- For use between 7C and 35C
- **Energy Usage Category A**

Unit must be vented outside when in AC and heater modes.
For the purposes of EU regulation EN12102 this is a "local air conditioner" and produces less than 65Db sound energy.



Free

**Window Kit
Included**

**Includes
Remote control unit**

TRADE BUYERS PHONE KOOLBREEZE ON 08 456 522 456

OR E-MAIL sales@koolbreeze.co.uk

See more of our range at www.koolbreeze.co.uk