



Multi Purpose



Light Duty

## Abrasion and tear-resistant gloves, offering good grip performance and high tactility

- **Enhanced durability:** Strengthened by PU coating, EDGE<sup>®</sup> 48-129 safety gloves offer EN level 4 abrasion resistance, good grip, and high tactility in dry to slightly oily environments
- **Augmented dexterity:** EDGE<sup>®</sup> 48-129 industrial gloves are composed of a seamless knitted liner and an elasticized knitwrist dipped into grey PU coating, which afford better flexibility and dexterity than cotton canvas and thick cotton gloves
- **Improved practicality:** Made of a grey 15-gauge polyester liner, these tear-resistant work gloves offer an efficient and economical light-duty glove solution



### Industries

- Automotive
- Electronics
- Oil and gas
- Machinery and Equipment
- Recycling and Waste Disposal
- Transportation

### Applications

- Assembly of small pieces
- General handling
- Packaging
- Quality inspection

### Key Features

- **Polyurethane coating:** Assured mechanical performance and protection
- **Seamless design:** Form-fitting flexibility, enhanced precision handling
- **15-gauge polyester liner:** For robust yet lightweight protective gloves

### Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4121A

### Specifications

| BRAND   STYLE            | DESCRIPTION                                                                                                                                | Gauge | SIZE              | LENGTH                        | COATING COLOR | PACKAGE                      |
|--------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|-------|-------------------|-------------------------------|---------------|------------------------------|
| EDGE <sup>®</sup> 48-129 | <b>Finishing:</b> Palm Coated<br><b>Coating Material:</b> Polyurethane<br><b>Liner Material:</b> Polyester<br><b>Cuff Style:</b> Knitwrist | 15    | 5, 6, 7, 8, 9, 10 | 215-270 mm, 8.46-10.63 inches | Grey          | 12 pairs/bag, 12 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, <sup>®</sup> and <sup>™</sup> are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.