

## M12 Y-cod 8-pol st/st m/m PUR 1.5m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 262 6840 015
Specification	M12 Y-cod 8-pol st/st m/m PUR 1.5m
HARTING eCatalogue	<a href="https://harting.com/21342626840015">https://harting.com/21342626840015</a>

### Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 Y-coding Male Straight
Connector 2	M12 Y-coding Male Straight
Type of cable	Copper cable (round)

### Version

Cable length	1.5 m
Number of cores	8
Core structure	4x AWG20 + 1x 4x AWG26
Coding	Y-coding

### Technical characteristics

Limiting temperature	-25 ... +80 °C
----------------------	----------------

### Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Green



**Pushing Performance**  
Since 1945

## Specifications and approvals

Approvals	CE
-----------	----

## Commercial data

Packaging size	1
Country of origin	Czechia
European customs tariff number	85444995
GTIN	5713140282629
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600