



2 YEARS
MANUFACTURER
GUARANTEE

400
+200 +120
LUMEN

6h
MAX.

USB C
CHARGER

IP20

USB RECHARGEABLE

0,6m

0,6m

Product number 1173730002
EAN 4007123691937

TECHNICAL DATA

Luminous flux	400 lm	Battery type	Special battery
Power consumption	3 W	Battery technology	Lithium-ion
Battery capacity	0.8 Ah	Impact strength	IK07
Battery voltage	3.7 V	Protection class	III
Light duration max.	6 h	Degree of protection (IP)	IP20
Battery charging time approx.	2.5 h	Colour	black/grey

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	0.18 kg
Weight of product (without packaging)	0.1 kg	Dimension LxWxH (incl. packing)	4.5 cm x 8.7 cm x 20.2 cm
Dimension LxWxH (without packing)	3.7 cm x 2 cm x 16 cm		