




MARKING:



WIRING COLOR:

- E: Green
- N: White
- L: Black

<p>LENGTH ON CORD: (613-14)</p> <p>(UL) E315167 SJT 60°C 3X18AWG(0.824mm²) 300V VW-1</p> <p>CSA LL81924 TYPE SJT 60°C 3X0.824mm²(18AWG) 300V VW-1</p>

No	BOM ITEM	Q' TY	P/N
1	∅4.75 BRASS TUBE	1 pcs	BPN47500
2	KWC-50T BLADE	2 pcs	BBN50T02
3	305 INNER BODY	1 pcs	MI305D00
4	305 OUT COVER	1 pcs	MI305U00
5	PVC 35P (SA93, SP-305B)	24 g	RPP03512
6	PE TIE (BLACK, 6 inch)	1 pcs	KBB10006

CABLE							SJT 18AWGx3C 60°C DENT PRINT CT-12 (BLACK)				
PLUG		SP-305B	LENGTH	2000	UNIT	mm					
CLIENT	NAME	First connectivity	N/W		UNIT	kg					
	P/N	7316204	SG DWG	SR-141239-2	VER.	A					
					Design. by	賀艷紅 (2014.05.23)					
					Review. by	朱曉玲 (2014.05.23)					
					Approval. by	周德雲 (2014.05.23)					
D5B JS3316							12	200	00		