

FEATURES

- 4 mm shrouded banana socket
- Nickel, tin-plated contacts
- 4.8 mm Faston connector
- Supplied with nut & washer
- Mates with shrouded or unshrouded plugs
- Available in multiple colours
- Pack of 5

RS PRO Female Banana Sockets - Tab Termination, 1000V, 24A

RS Stock No.: 191-7888, 191-7889, 191-7891



191-7888

191-7889

191-7891

RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Banana Connectors

Product Description

Introducing a series of banana sockets from RS PRO. These female socket connectors mate with the popular 4 mm shrouded or unshrouded banana plugs. Upon inspection, these connectors have a shrouded female socket at one end with nickel/ tin-plated contacts, an M12 x 0.75 threaded body, and a 4.8 mm faston tag at the other. They operate at a high voltage (1kV) and have a 24 A current rating. Supplied with nut & washer.

General Specifications

- 4 mm shrouded banana socket
- Nickel, tin-plated contacts
- 4.8 mm faston connector
- Supplied with nut & washer

Mechanical Specifications

Cut-out diameter	M12 x 0.75
Diameter	14.5 mm
Length	24.5 mm

Electrical Specifications

Current rating	24 A
Rated	1000V

Protection Category

CAT	III
-----	-----

Classification

eCl@ss (Version)	
UNSPSC (Version)	

Approvals

Declarations	
Hazardous Area Certification	
Standards Met	

Similar Products

Stock No.	Brand	Product Name	Colour		
224-7423	RS PRO	RS PRO 4 mm Banana Socket - Female	Black		
224-7424	RS PRO	RS PRO 4 mm Banana Socket - Female	Green		
224-7427	RS PRO	RS PRO 4 mm Banana Socket - Female	Red		

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories