



423.3266

FLUSH-MOUNTING SOCKET

32A 3P+E 6h 380-415V 50Hz 60Hz 75X75MM
Screw terminals

Product Approvals

| TECHDATA | | STANDARDS AND LAWS | |
|----------------------------|-----------------------|-----------------------------------|---|
| Commercial series | OPTIMA Series | EN 60309-1 (1999) | [European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements |
| Type of product | FLUSH-MOUNTING SOCKET | EN 60309-2 (1999) | [European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations |
| Synthetical description | FLUSH-MOUNTING SOCKET | | |
| Mounting version | FLUSH MOUNTING | EN 60309-1/A1 (2007) | [European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements |
| Rated current | 32A | EN 60309-2/A1 (2007) | [European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations |
| Poles | 3P+E | | |
| Hour position | 6h | | |
| Rated voltage (range) | 250-400V | EN 60309-1/A2 (2012) | [European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements |
| Rated voltage | 380-415V | EN 60309-2/A2 (2012) | [European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations |
| Working frequency | 60Hz | | |
| Working frequency | 50Hz | | |
| Colour | RED | DIRECTIVE LOW VOLTAGE 2014/35 /UE | [European Directives] Low Voltage Directive |
| Material | THERMOPLASTIC | | |
| Protection degree | Splash proof | | |
| Protection degree IP | IP44/IP54 | | |
| Types of available outlets | STRAIGHT | | |
| Terminals | Screw terminals | | |
| Flange | 75X75MM | | |

