

DCD777D2T-QW

XR 18V 2Ah Li-Ion Brushless Drill Driver - Plastic Chuck



5035048690444



Product Description:

Hard/Soft Torque (Nm): 65/26 No-load speed (rpm): 0-500/1750 Ø Wood/Metal Drilling (mm): 30/13 Chuck Capacity (mm): 1.5-13 Plastic Chuck

Product features and benefits:

- 13 mm mandrel
- 2 speed settings, variable speed and inverter for maximum Efficient intelligent triggering for full control over
- All applications
- 16 torque adjustment positions for optimal precision LED light for better visibility Ergonomic design and rubber grip improving user comfort
- Multi-voltage charger included Part of the XR Intelligent Li-ion platform, designed to deliver even more efficiency and speed

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Specifications techniques :

- **Capacity** (wood):
 - Couple maximal : 65 Nm
 - **Capacity** Battery: 2.0 Ah
 - **Voltage** 18V
 - Weight (including battery): 1.55 Kg
 - **Power**: 340 W
 - **Drilling Capacity (Metal):** 13 mm Chuck Capacity: 1.5-13 mm

