

PRODUCT-DETAILS

# N4NY-004-0-C

## CABLE CLAMP BLK PLAIN EDGE .25 DIA



### General Information

Extended Product Type	N4NY-004-0-C
Product ID	7TAG009970R0062
EAN	5414363033905
Catalog Description	CABLE CLAMP BLK PLAIN EDGE .25 DIA
Long Description	Plain Edge Cable Clamp, Black Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Width of 9.53mm (0.375 Inches), Thickness of 1.27mm (0.50 Inches), Hole Diameter of 4.3mm (0.170 Inches), #8 Screw Mounting with Closed Diameter of 6.3mm (0.25 Inches)

### Ordering

EAN	5414363033905
UPC	728494090337

### Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	10000 piece
Package Level 2 Width	13 in 330 mm
Package Level 2 Height	13.5 in 343 mm
Package Level 2 Depth / Length	18 in 457 mm

---

## Additional Information

Brand / Label	Ty-Rap
Color	Black
Effective Date	19960215
Material	Nylon/Polyamide 6.6
Mounting Type	#8 Screw
Number of Batteries	0
Product Name	NYLON CABLE CLAMP
Product Type	Plain Edge Cable Clamps
Special Functions	Fully radiused inside edges with size markings in inches and millimeters for easy identification.

---



---

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	N4NY-004-0-C
Instructions and Manuals	N4NY-004-0-C
REACH Declaration	9AKK107992A8792
RoHS Information	9AKK107992A8811

---



---

## Classifications

ETIM 6	EC000127 - Saddle
ETIM 7	EC000127 - Saddle
UNSPSC	39121702
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5029 >> Nylon Cable Clips

---



---

## Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

