

**Manifold block**  
**VABM-B10-25E-N12-5-P3**  
Part number: 8026291

**FESTO**



 [General operating condition](#)

**Data sheet**

| Feature                        | Value                         |
|--------------------------------|-------------------------------|
| Grid dimension                 | 27.5 mm                       |
| Mounting position              | optional                      |
| Max. number of valve positions | 5                             |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity         | VDMA24364-B1/B2-L             |
| Product weight                 | 1428 g                        |
| Type of mounting               | With through-hole             |
| Pilot air port 12              | 1/8 NPT                       |
| Pneumatic connection, port 1   | 1/2 NPT                       |
| Pneumatic connection, port 3   | 1/2 NPT                       |
| Note on materials              | RoHS-compliant                |
| Material manifold rail         | Wrought aluminium alloy       |