



Flexible Cable Support

Heladuct flexible cable supports are commonly used in switching cabinets. They are also used in the furniture industry, where cables need to be routed rapidly and attractively.

Features and benefits

- Space-saving wiring system
- Highly flexible, can be installed at angles of 90° and higher
- Cable clearly open to view
- Rapid mounting with screws or adhesive strip with high-quality foam bonding layer



Heladuct Flex- clearly and space-saving arrangement of wiring, even at angles above 90°.

MATERIAL	Polypropylene (PP)
Operating Temperature	-20 °C to +70 °C, (+80 °C, 200 h)
Adhesive	Synthetic rubber with base of polyethylene foam
Flammability	UL 94 V0 (excluding adhesive)



Heladuct Flex Screw Mounting

TYPE	Nominal Ø	Fixation Method	No. of Wires		Colour	Length (L)	Pack Cont.	Article-No.
Heladuct Flex10	10	Screw Mounting	6 x 1.50 mm ²	4 x 2.50 mm ²	White (WH)	500	100 pcs.	164-11008
Heladuct Flex20	20	Screw Mounting	22 x 1.50 mm ²	14 x 2.50 mm ²	White (WH)	500	70 pcs.	164-21008
Heladuct Flex30	30	Screw Mounting	50 x 1.50 mm ²	34 x 2.50 mm ²	White (WH)	500	40 pcs.	164-31008
Heladuct Flex40	40	Screw Mounting	81 x 2.50 mm ²	60 x 2.50 mm ²	White (WH)	500	24 pcs.	164-41008

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.

Heladuct Flex Screw Mounting with Adhesive

TYPE	Nominal Ø	Fixation Method	No. of Wires		Colour	Length (L)	Pack Cont.	Article-No.
Heladuct Flex10SK	10	Screw Mounting and Adhesive	6 x 1.50 mm ²	4 x 2.50 mm ²	White (WH)	500	100 pcs.	164-11108
Heladuct Flex20SK	20	Screw Mounting and Adhesive	22 x 1.50 mm ²	14 x 2.50 mm ²	White (WH)	500	70 pcs.	164-21108
Heladuct Flex30SK	30	Screw Mounting and Adhesive	50 x 1.50 mm ²	34 x 2.50 mm ²	White (WH)	500	40 pcs.	164-31108
Heladuct Flex40SK	40	Screw Mounting and Adhesive	81 x 2.50 mm ²	60 x 2.50 mm ²	White (WH)	500	24 pcs.	164-41108

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.