


FAG

UCP213

Plummer block housing unit

Plummer block housing units UCP, cast iron housing, with long base, radial insert ball bearing with grub screws in inner ring, RSR seals

Technical information



Your current product variant

Material	GG	Grey cast iron
Housing clearance	J7	Normal swivel torque

Main Dimensions & Performance Data

d	65 mm	Bore diameter
L	265 mm	Length total
H ₂	151 mm	Height
≈m	5.55 kg	Weight

Mounting dimensions

J	203 mm	Distance fixing bore
N	25 mm	Width (slot)
N ₁	29 mm	Length (slot)

Dimensions

H	76.2 mm	Distance shaft axis
A	70 mm	Width (base)
H ₁	27 mm	Heigth (base)
B	65.1 mm	Width
S ₁	39.7 mm	Distance of raceway to locking collar
Q	M6	Connection thread for lubrication



Additional information

P213	Housing
UC213	Bearing designation

Temperature range

T _{min}	-20 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.