



ENGLISH

Datasheet

RS Pro Anti surge T LBC fuse, 3.15A 5 x 20mm BP

RS Stock No: **563-621A**



Product Details

RS Pro anti surge LBC fuse is current rated for 3.15 A. This glass bodied, T-speed fuse is used as supplementary protection in appliance or utilisation equipment to provide individual protection components or internal circuits.



Specifications:

Body Material	Glass
Breaking Capacity (at Maximum Voltage Rating)	35 A
Current Rating	3.15 A
Diameter	5.2 mm
Fuse Speed	T
High Rupture Capacity	No
Includes Indicator	No
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-55°C
Operating Temperature Range	-55 to +125°C
Overall Dimensions	5.2 x 20 mm
Overall Length	20 mm
Resistance	0.0187 Ω
Size Designation	Miniature
Voltage Rating	250 V ac
Standards Met	CSA Acceptance, UL Recognised, RoHS Compliant, CCC, UTE, PSE, KTL, CQC, TUV, VDE, BSI, SEMKO Approved