

PREVOST FILTRATION - UNIT COMBINATIONS

Filter regulator with manual valve - 2 units



Part number	Female thread	Pressure (bar)	Flow rate at 6.00 bar (l/min) ($\Delta P = 1.00$ bar)	Max. operating pressure (bar)	Filtration (μm)	Net weight (Kg)
ATU VM2585101	G1/4	6.00	1000.00	10.00	25.00	0,48
ATU VM2585102	G3/8	6.00	3000.00	10.00	25.00	1.88
ATU VM2585103	G1/2	6.00	4500.00	10.00	25.00	1.88