

Datasheet

MA05/10 Series 240V dc SMD Power Line Filter

RS Stock number [206-7904](#)



Specifications:

- Depth: 52mm
- Dimensions: 85 x 52 x 40mm
- Height: 40mm
- Length: 85mm
- Max. Current Rating: 10
- Max. Operating Temperature: +85°C
- Max. Voltage Rating: 240 V dc
- Min. Operating Temperature: -25°C
- Mounting Type: Surface Mount
- Operating Frequency: 50/60Hz
- Termination Style: Fast-On