


STO15

Galet de roulement

Yoke type track rollers STO..., single row needle roller bearings with particularly thick-walled outer ring, needle roller and cage assembly and an inner ring, without axial guidance of the outer ring, open, inner ring, outer ring and needle roller and cage assembly can be mounted separately

Information technique



Votre alternative produit actuelle

joint	Sans	
profile bague extérieure	R500	Diamètre extérieur sphérique (Standard)
dispositif de lubrification	IR	Via inner ring lubrication hole

dimensions principale & données de performance

d	15 mm	Alésage
D	35 mm	Diamètre extérieur
C	11,8 mm	Largeur, bague extérieure
C _{r w}	9.100 N	Charge dyn. de base, radiale
C _{0 r w}	11.100 N	Charge stat. de base, radiale
C _{ur w}	1.670 N	Limite à la fatigue, radiale
n _{D G}	3.300 1/min	Vitesse pour une lubrification à la graisse
≈m	63,1 g	Poids

Dimensions

B	12 mm	Largeur, bague intérieure
E	26 mm	Diamètre de piste bague extérieure
r _{min}	0,3 mm	Dimension minimum de chanfrein
F	20 mm	Diamètre de piste bague intérieure
R	500 mm	Rayon bague extérieure profile externe



Caractéristiques



Effort radial



Lubrification à la graisse



lubrification à l'huile



Ouvert