

Datasheet

LED SINGLE 6Ft BATTEN 840

Stock No: 216-9734



Technical Specifications:

Length	1800mm
Width	63mm
Height	74mm
IP20 Steel body with polycarbonate opal LED diffuser. 4000K	Single row of SMD LEDs on metal core PCB


Applications

- For commercial or domestic applications
- Non-emergency versions rated from -20°C - +25°C

Features & Benefits:

- Flicker Free driver
- 50W / 6040lm 124 l.lm/c.W
- Piano key terminal block
- 5 years warranty

Dimensional line drawings



Quality Standards

- EN 55015 Emissions from lighting equipment
- EN 61547 Immunity of general lighting equipment
- EN 61000-3-2 Mains harmonic equipment up to 16A
- EN 61000-3-3 Voltage fluctuations equipment up to 16A
- EN 60598-2-1 Fixed general purpose luminaires
- EN 60598-2-22 Particular requirements for emergency luminaires

General

LUMINAIRE PERFORMANCE

Luminaire Lumens (lm)	6040
Power Consumption (W)	50
Efficacy (l.lm/c.W)	124
Operating Temp. (Min/Max)	-20/+25

LIGHT SOURCE

Type	LED
Correlated Colour Temp.	4000
Colour Rendering Index (CRI)	>80
Lumen Depreciation	L70:B10 50000
SDCM	<5

ELECTRICAL INPUT

Voltage (V)	220-240V AC
Operating Frequency (Hz)	50
Inrush	<25A
Class	Class 1
Power Factor (PF)	>0.95
Cable Entry	Side /Base

ELECTRICAL OUTPUT

Forward Current (mA)	-
Forward Voltage (Vf)	-