
2104 : Stainless Steel Pipe Cutter 6-28 mm











Description

Max thickness: 3.2 mm.
Soft Touch® non-slip knob: good hold in hand.
Quick and tool-less wheel change.
Fold-away reamer blade.

References

Sku	A mm	A " OD	L mm	H mm	E maxi mm	kg
210469	6 - 28	1/4 - 1.1/8	142	55	3,2	0,385

