

Angle Grinder XGT® 125mm

GA029G

40V max • 125 mm • 3 000 – 8 500 min⁻¹

Efficient brushless tool with brake for cutting and grinding

Brushless, paddle switch angle grinder with a 125 mm wheel for demanding professional use. Adjustable speed from 3 000 – 8 500 min⁻¹ by using variable speed control dial. AWS remote vacuum cleaner start function.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
No load speed	3000 - 8500 min ⁻¹
Spindle Thread	M14
Bore Size (Arbor Diameter)	22,23 mm
Disc Diameter	125 mm
Anti-Restart Function (NVR Switch)	✓
Electronic brake	✓
AWS ready	✓
Sound Power Level (L _{WA})	93 dB(A)
Sound Pressure Level (L _{pA})	85 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Tool weight with battery	3,0 - 5,4 kg

User benefits

- Outperforming performance and efficiency similar to corded 1 000 W class grinder
- Genuine solution for high demand industrial applications
- Excellent in continuous heavy-duty work
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Electric brake for maximum productivity and increased operator safety
- Paddle switch; Easy-to-hold slim grip achieved by optimised parts allocation
- Anti-restart function minimises accidental start-up
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection system automatically shuts off power when the battery level is low
- Soft start for smooth start-ups

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing