

# NTT01

## 24 Hour Compact Immersion Heater Timeswitch

### Features & Benefits

- 96 Quick-Set Segments for up to 48 ON/48 OFF Programmes Per 24 Hrs
- Red LED 'Mains ON' and Green LED 'Output' Indicators For Easy Viewing
- 'Traffic Light' Slide Switch for Easy ON (green), Auto (green & red) and OFF (red) Mode Indication
- Switches ON and OFF at Preset Times
- Easy to Use Captive Segment Dial
- Permanent ON/OFF Control
- Fits a Standard Flush or Surface Mount Box min 32mm



### Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Surface Mount
Earth Class Rating	Class II
Operating Temperature	0°C to 40°C
Ingress Protection Rating	IP20
Setting Type	Segment
Back Box Minimum Depth (mm)	32

# Data sheet

## NTT01

Time / Immersion & General Purpose Timeswitches

Program Modes	24 Hour
Switch type	Single Pole
Mounting Hole Centres (mm)	60
Standby Consumption	<1.43W
Number of Channels	1
Switch rating	16A Resistive 6A Inductive, 100W LED
Shortest Switching Time	15 Minutes
Programmable Slots	48 ON 48 OFF (96 Segments)
Permanent ON Facility	Yes (Slider Switch)
Cable Capacity (mm <sup>2</sup> )	1.5 - 2.5mm <sup>2</sup> Flexible Cable
Cable Entry(s)	Back Entry

### General

Weight (g)	160
Height (mm)	92
Width (mm)	92
Depth (mm)	60
Body Construction	Polycarbonate
Product Colour	White
Accessories (Included)	Fittings (Rawl Plugs, Screws)
EAN Number	5012483012291
Guarantee Period	3 Years

# Data sheet

## NTT01

Time / Immersion & General Purpose Timeswitches

### Line Diagrams

