

WML 22 (35X25)A4 - Cable marker label



0830695

<https://www.phoenixcontact.com/gb/products/0830695>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker label, Sheet, white, unlabeled, can be labeled with: Office printing systems, CMS-P1-PLOTTER, PLOTMARK, cable diameter range: 8 ... 21.3 mm, mounting type: adhesive, cable diameter: ≤ 21.3 mm, Number of individual labels: 10, text field height: 25.4 mm, text field width: 35 mm

Your advantages

- For indoor applications: high resistance to dirt and abrasion due to the protective laminate
- Firmly defined positioning of labels thanks to the adhesive system
- Broad diameter range with many different applications inside and outside the control cabinet
- The protective foil is wound over the labeling and provides permanent protection against dirt and abrasion
- The wrap-around labels do not create any additional volume, so the cable can also be pulled through cable ducts, for example
- For cylindrical objects, single wires, and cables

Commercial data

Item number	0830695
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG2314
Product key	BG2314
Catalog page	Page 216 (C-3-2019)
GTIN	4046356718806
Weight per piece (including packing)	14.5 g
Weight per piece (excluding packing)	14.48 g
Customs tariff number	39199080
Country of origin	DE

WML 22 (35X25)A4 - Cable marker label



0830695

<https://www.phoenixcontact.com/gb/products/0830695>

Technical data

Notes

General	Print image may vary depending on laser printer
---------	---

Product properties

Product type	Conductor marking
Type	Label

Marking

Number of individual labels	10
Number of individual labels per row	5
Identification technology	Office laser printing

Dimensions

Width	35 mm
Length	92.25 mm

External dimensions

Outside diameter	8 mm ... 22 mm
------------------	----------------

Text field

Text field width	35 mm
Text field height	25.4 mm

Material specifications

RoHS compliant	yes
Adhesive	Acrylic
Color	white (RAL 9010)
Material	Polyester
Components	Free from halogen and cadmium

Cable/line

External cable diameter	≤ 21.30 mm
	8 mm ... 21.3 mm

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

WML 22 (35X25)A4 - Cable marker label



0830695

<https://www.phoenixcontact.com/gb/products/0830695>

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Ambient temperature (storage/transport)	23 °C
Permissible humidity (storage/transport)	50 %
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

WML 22 (35X25)A4 - Cable marker label



0830695

<https://www.phoenixcontact.com/gb/products/0830695>

Classifications

ECLASS

ECLASS-11.0	27281102
ECLASS-12.0	27281102
ECLASS-13.0	27281102

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

WML 22 (35X25)A4 - Cable marker label



0830695

<https://www.phoenixcontact.com/gb/products/0830695>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

info@phoenixcontact.co.uk