



Main

Range	Resi9
Product or component type	Control panel
Accessory / separate part category	Installation accessory
Network connection	Three phase
Quantity per set	1

Complementary

Range compatibility	Opale Resi9
[In] rated current	90 A
Enclosure mounting	Wall mounted
9 mm pitches	26
Total number of 18 mm modules	13
Net weight	1.35 kg
Width	250 mm
Height	550 mm
Depth	58 mm
Colour	White (RAL 9003)

Environment

Product certifications	ERDF CPT M&S SPE 13006A
Electrical insulation class	Class II
Fire resistance	750 °C conforming to IEC 60695-2-11
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations