



# PRODUCT DATASHEET

Datasheet creation date: 2025/07/09 7:35 (UTC)



## 607

### Extra Small Ball Bearings and Miniature Ball Bearings Metric Series



#### Boundary Dimensions

d	7	mm	Bore diameter
D	19	mm	Outside diameter
B	6	mm	Width
r (min.)	0.3	mm	Chamfer dimension

#### Basic Load Ratings

Cr	2570	N	Basic dynamic load rating
C0r	885	N	Basic static load rating

#### Speeds

Grease	36000	min-1	Grease lubrication
Oil (Oil-bath)	43000	min-1	Oil-bath lubrication

#### Abutment and Fillet Dimensions

da (min.)	9	mm	Diameter of shaft abutment
Da (max.)	17	mm	Diameter of housing abutment
ra (max.)	0.3	mm	Radius of shaft or housing fillet

#### Additional information

z	6		Number of Balls
Dw	3.5	mm	Ball Diameter

#### Mass

Mass approx.	0.00767	kg	Mass approx.
--------------	---------	----	--------------

