

LAPTOP 3200 ELECTRONIC SERVICE CASE

The professional combination of Laptop Bag and Tool Case



3200 **BERNSTEIN** Laptop with tool tray, with tool set

3215 **BERNSTEIN** Laptop with tool tray, without tool set

3255 **BERNSTEIN** Laptop without tool tray, without tool set

Description:

Elegant Laptop and Tool Case made from black nylon, with inside pad and reinforced frame. The bag is divided in 2 zip-fastener bags and has loops on both sides for attaching the shoulder strap.

The tray in the upper zip-fastener bag is prepared for the arrangement of a Laptop, together with the necessary accessories, e.g. connector cable, power supply and mouse. The lid of this bag is provided with several pockets for CDs, USB-sticks, writing utensils and documentations.

The design 3200 additionally is equipped with a tool tray accurately arranged with 28 special tools. This removable tray is fastened in the case as a swivel-tool-tray with hook-and-loop tape.

The bottom zip-fastener bag, with 3 partitions, is mainly provided for documents and literatures.

Outside dimensions: 480 x 380 x 140 mm (when closed)

Weight with tools: approx. 3.550 kg

Tool set:

No.	Description of individual tools
1-552	Adjusting screwdriver , 2 x 0.4 x 120 mm
2-126	Desoldering bar , slotted at one end, nickel-plated, insulated, with plastic handle
2-127	Tin knife with pointed, sharp blade, high quality steel, for cutting circuit paths and for burring
2-166	Glass fibre contact cleaner brush with rotary mechanism, plastic casing
2-265	2 Test prods , red and black, extremely slim, pointed and flexible, blade made from 1 mm steel wire
2-275	Repair mirror , 21 mm Ø, with handle, 180 mm long
2-601	IC tweezers , nickel-plated, 125 mm, for gripping, inserting and removing IC's
2-620	PLCC extractor for easy removal of plug-in PLCC's
3-109-2	Side cutters , 120 mm, with wide, rounded head, without side face, chrome-plated, with transparent insulation
3-127-2	Slimline side cutters , 115 mm, for soft wire up to 1 mm, extremely slim head, box joint, compression spring, chrome-plated, with transparent insulation
3-445-2	Micro flat nose pliers , 120 mm, extremely slim, box joint, chrome-plated, with transparent insulation
3-481-2	Snipe nose pliers , 120 mm, angular, box joint, compression spring, chrome-plated, with transparent insulation

No.	Description of individual tools
3-565	Water pump pliers , 130 mm, chrome-plated
4-142	Screwdriver to DIN 5265, with special square pattern BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, with black tip, 100 x 4 mm
4-406	Retaining screwdriver , 80 x 4 mm, vernickelt
4-901	Interchangeable screwdriver set
4-905	ESD handle with brass clamping sleeve
4-906	Hexagon blade widths 1.5 / 3.0 mm, matt chrome-plated, black tip
4-907	Hexagon blade as above, widths 2.0 / 3.5 mm
4-911	Hexagon blade as above, widths 2.5 / 4.0 mm
4-912	Hexagon blade as above, cross-recess PH 000 / PH 00
4-921	Hexagon blade as above, cross-recess PH 0 / PH 1
4-922 L	Hexagon blade as above, TORX T 5 / T 6
4-923 L	Hexagon blade as above, TORX T 7 / T 8, with bore hole
5-051	Hexagon blade as above, TORX T 9 / T 10, with bore hole
5-107	SMD-tweezers , 115 mm, straight, pointed, anti-magnetic, stainless, matt finish, acid-resisting
5-301	Steel tweezers with bent tips, 150 mm, nickel-plated
	Special scissors for cutting sheet-metal and wires, with serration, extremely slim, 110 mm, nickel-plated