



**fitted with**

**work equipment**  
**connected load**  
**power consumption**  
**light distribution**  
**system of protection**  
**class of protection**  
**luminaire body**  
**weight (net)**  
**mains supply**

**fastening**  
**dimension**  
**light output**  
**outside diameter**  
**side part**

1 x compact fluorescent lamp TC-LEL 24W/840 2G11  
 light colour neutral white  
 Energy efficiency category B  
 electronic ballast  
 24 V; 50/60 Hz  
 approx. 24 W  
 direct  
 IP 67  
 III  
 acrylic (PMMA), clear,  
 approx. 1.6 kg  
 connection box  
 160 BU/3  
 lamp bracket (accessory)  
 A=639 mm  
 D=317 mm  
 70 mm  
 C with screwed cable gland



160 BU/3

**illuminance**

Comment: d=100cm

Em: 259 lx  
 Emax: 333 lx  
 Emin: 178 lx

