



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Device presentation	Basic element with full cover plate
Device application	Control
Colour	Cover: grey
Handle colour	Red
Suitability for isolation	Yes

Complementary

Switch function	3-pole
Poles description	3P
Control type	Rotary knob
Number of poles	3
Device mounting	Surface
Fixing mode	By screws
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	40 A
Breaking capacity	40 kA
Motor M-rating AS3133	M220 at 690 V
Rotary handle padlocking	2 padlocks 8 mm
Marking	Without marking
Height	204 mm
Width	101 mm
Depth	172 mm
Net weight	1.1 kg
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

Packing Units

Package 1 Weight	1.100 kg
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile