




Main

Product or component type	Neutral bar
Enclosure type	Standard
Door type	Overall

Complementary

[Ie] rated operational current	250 A at 400/415 V AC
Breaking capacity	25 KA
Poles description	3P + N
Protection device name	IC60H
Product destination	Distribution board
Number of ways	4 ways outgoer
Provided equipment	Neutral bar Busbar link 4 Cover
Enclosure material	Steel
Surface treatment	Epoxy
Surface finish	Powder paint
IP degree of protection	IP2X internal conforming to BS EN 60529 IP3x external conforming to BS EN 60529
IK degree of protection	IK05 conforming to BS EN 60529
Colour	White (RAL 9001)
Height	484 Mm
Depth	138 Mm

Environment

Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.0 Cm
Package 1 Width	8.5 Cm
Package 1 Length	38.0 Cm
Package 1 Weight	252.0 G

Unit Type of Package 2	PAM
Number of Units in Package 2	175
Package 2 Height	112 Cm
Package 2 Width	100 Cm
Package 2 Length	120 Cm
Package 2 Weight	100 Kg

Environmental data

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**