



ENGLISH

Datasheet

Stock No: 429-688

RS Pro PE Flexible Conduit Grey 10mm IP55 5m



Product Details

IP55 conduit

A low cost flame retardant, general purpose conduit resilient to prolonged flexing and vibration. Manufactured from extrusion drawn polyethylene.

IP55 conduit (when used with compatible fittings, available separately)

Conduit -50 → 100°C, fittings -25 → 50°C operating temperature

Crush resistant to BS6099

Resistant to: nitric acid, sulphuric acid, detergent, diesel and white spirit



ENGLISH

Specifications:

| | |
|-------------------------------|----------|
| Nominal Diameter | 10mm |
| Conduit Type | Flexible |
| Material | PE |
| Colour | Grey |
| Interior Diameter | 7.4mm |
| Outer Diameter | 10.2mm |
| Length | 5m |
| IP Rating | IP55 |
| Minimum Operating Temperature | -50°C |
| Maximum Operating Temperature | +100°C |
| Minimum Bend Radius | 9 mm |

