



REV	DOCUMENT	CHANGED BY	CHECK
B	0069593	VKK 27SEP10	CMH



DESIGN UNITS: INCH TOLERANCES UNLESS NOTED:				DRAWN	KMJ	17MAR00	<b>Honeywell</b>					
				CHECK	—	—						
NO PLACES	X	±	—	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE PRESSURE SWITCH N.O. BLADE TERMINALS 5000 SERIES SWITCH					
ONE PLACE	.X	±	.020									
TWO PLACE	.XX	±	.020									
THREE PLACE	.XXX	±	.005									
ANGLES	X	±	0° 30'	INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	CAGE CODE	DRAWING NAME		REV
THIRD ANGLE PROJECTION 							B	E	—	83282		B
				AUTOCAD 2D			SCALE	2:1			SHEET	1 OF 1