

# Edge protection profile E8

Article number	1127130	Sales unit quantity	5 Piece
Colour	Yellow / black	Sales unit EAN	4005546735849
Packaging unit	5 pieces / pack	Packing weight (gross)	1710 G
Base EAN	4005546735832	Country of origin	CN



## Product description

- Self-adhesive, flexible edge protection profile made of polyurethane foam
- For indoor use only
- Ideal for securing shelves, sharp edges, T-beams etc. in manufacturing, shipping areas and warehousing, basements, stairwells and garages.
- Marks danger spots, mitigates impact injuries and prevents damage to vehicles and transport trolleys.
- Profiles can be shortened to the desired length with a sharp cutter knife
- Colour according to ASR A1.3 similar to RAL 1004/9003 (signal yellow/signal black)
- Fire test according to DIN EN 13501-1:2018-12 class E
- Temperature resistant from -30°C - + 70°C
- Profile length: 1 m
- Width cut-out: 8 mm

## Product features

Outer width (mm)	25
Outer height (mm)	30
Outer depth / length	1,000 mm
Brand	DURABLE
Inner width (mm)	8
Inner height (mm)	19

# Edge protection profile E8

Self-adhesive type	Permanent
Material thickness	7 mm
Special colour	Similar to RAL 1003 signal yellow / 9004 signal black
Application area	Indoor area, protected outdoor area
Mounting type	Self-adhesive