

Limit Switch Style Proximity Sensor

USPs:

- Replacement for Mechanical Limit Switches, same footprint
- Range of sensing distance options to suit the application requirements
- Very bright indication LEDs, corner mounted to visible from any angle
- Superior EMC interference immunity
- Wide operating temperature range -25°C to 85°C
- Easy replacement, terminal base can be left in situ, no rewiring required
- Adjustable sensing face; Left right, up, down and forward
- Robust, waterproof & UV resistant

Excellent choice
- Market leader since 1958

Easy installation
- Standardized terminal base

Compact dimensions
- 1 head for many operating distances

Weatherproof
- Robust, water proof, UV resistant

Highly versatile
- Designed for indoor and outdoor use

Temperature resistant
- Temperature range -25 °C to +85 °C

Superior EMC
- Simplified planning

Cosmopolitan
- Now available as R1 version

4 LEDs
- Visible from all angles

www.a-level-higher.com
PEPPERL+FUCHS