

## A5500/1, NS100, 0...120°C, L1=200x8mm

### Bimetal thermometer, stainless steel version

Item number: 3906361

Quantity: 1 pcs.

Order code: A5500 -1-C1F-BK-C200GZZ-ZZZZZZ TB FZZZEPZSVID-  
AZ1ZZZZZ2ZZZZ

Overview: A5500/1, NS100, 0...120°C, L1=200x8mm  
Process connection: plain, without thread, axial  
flat instrument glass,  
class 1 per EN 13190  
with Serial number  
\*WIKA\*

Details: Bimetal thermometer, stainless steel version  
Specifications according to data sheet: TM 55.01  
Case: stainless steel  
Stem material: stainless steel  
Model: A 5500, nominal size 100, location of stem centre back (axial)  
Connection design: 1, plain stem  
Unit: °C  
Scale range: 0 °C ... 120 °C  
Process connection: plain, without thread  
Stem diameter: 8 mm  
Insertion length L1: 200 mm  
Window: flat instrument glass  
Case: Stainless steel  
Connector location: axial  
Version: standard  
Stem material: stainless steel  
Permissible ambient temperature: -40 ... +70 °C  
Manufacturer logo: \*WIKA\*  
Accuracy class: class 1 per EN 13190  
Ingress protection: IP 65  
Serial number: with Serial number