



mecalectro

Small linear solenoid for standard use – 8.M10.02.62



Stroke: 7 mm

Force at beginning of stroke (FM: 100/25/5%):
0.1/0.3/1.6 N

Force at end of stroke (FM: 100/25/5%):
0.6/2/3 N

Power Consumption (FM: 100/25/5%):
2/7/31 W

Total mass: 20 g

Degree of protection / Energetic class: IP 00 / B
Standard supplies: 24Vcc

Possible supplies: From 6 to 24Vcc

Duty Cycle: Permanent, impulses (100 / 40 / 25 / 15 / 5 %)

Standard: NF C 79300

Examples of applications: Various automations, setting in position, multiple locks.