



MY4N-GS-R DC24

Relay, plug-in, 14-pin, 4PDT, 6 A, mechanical & LED indicators, 24 VDC

Specifications

Mounting method	With plug-in socket
Usage	General purpose
Poles	4
Rated carry current	6 A
Coil voltage	24 V
Operation voltage	DC
Contact material	Ag
Contact description	4PDT
Features	LED, Transparent case, With mechanical indicator
Terminal type	Plug-in

Fits to



PY14-02

Socket, back-connecting, 14-pin, PCB terminals



PYF-14-PU

Socket, DIN rail/surface mounting, 31 mm, 14-pin, Push-in terminals



PYF14A-N

Socket, DIN rail/surface mounting, 14-pin, screw terminals (IEC/VDE)



PYFZ-14-E

Socket, DIN rail/surface mounting, 14-pin, screw terminals (standard)



Industrial Relays Brochure

EN PDF 2.77 MB



MY-GS- R/MY(s)/MYK/MYQ/MYH Miniature Power Relays

Datasheet

EN PDF 20.3 MB



OMRON Manufacturing Know-How: High Quality Relays

Leaflet

EN PDF 449 KB



Solution case study No.8 Environment resistance

Brochure

EN PDF 623 KB