

Features

- Accepts cable diameters of upto 14mm
- Can be used with a maximum panel thickness of upto 4mm Thick.
- REACH and ROHS Compliant

RS PRO Black Polychloroprene 20mm Open Cable Grommet for Maximum of 14mm Cable Dia

RS Stock No.: 0428028



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This 20 mm round open cable grommet from RS PRO is designed for easy installation, providing protection for wires while ensuring a tidy finish. To use, simply cut a hole to the required size, insert the grommet into the panel, and feed the cable through the pre-formed opening.

It accommodates cables with diameters between 1 mm and 14 mm, offering a secure and flexible routing solution. This grommet is compatible with panels up to a maximum thickness of 4 mm, helping to reduce cable strain and minimise wear.

Made from black polychloroprene rubber, it is suitable for temperatures ranging from -30°C to +90°C.

Specifications

Grommet Type	Cable Grommet
Material	Polychloroprene
Colour	Black
Maximum Panel Thickness	4mm
Minimum Cable Diameter	1mm
Maximum Cable Diameter	14mm
Panel Hole Diameter	20mm
Minimum Operating Temperature	90°
Maximum Operating Temperature	-30°

Approvals

Standards Met	REACH, RoHS
---------------	-------------