



ENGLISH

Datasheet

LED Inspection Light



RS Article No. :

RS STOCK NO	DESCRIPTION	A	C	D	ψ
777-7934	AC/DC24V, 1Wx6pcs, unterminated	380m/m	396m/m	414m/m	70
777-7996	AC100V-240V, 1Wx6pcs UK plug	380m/m	396m/m	414m/m	70
777-7946	AC100V-240V, 1Wx6pcs EU plug	380m/m	396m/m	414m/m	70
777-7943	AC100V~240V, 1Wx12pcs	658m/m	674m/m	692m/m	70
777-7990	AC100V~240V, 1Wx12pcs UK plug	658m/m	674m/m	692m/m	70
777-7940	AC100V~240V, 1Wx12pcs EU plug	658m/m	674m/m	692m/m	70

Features:

Beam angle: 80°

Approval: CE

Protection rating: IP67

Outer Tube: Glass lens

Cable: 1.8 m (fitted with plug where applicable, see table above)

Diagram:

