



Ball joint, K8967S

Drive: 3/4" DIN 3121H 20, ISO 1174.

Finish: forged, phosphated.

Material: VANADIUM-EXTRA.

Maximum angle 35°.

With through hole



1268329



1



3/4"



3/4"



98



48 K560F-6 670

K8967S