



Domestic dehumidifiers that are compact, portable and easy to move and setup. Available in 4 versions, according to dehumidification capacity: 12L., 16L., 20L. and 30L.

Features

Super-silent rotary compressor.
Electronic humidistat, allowing you to select the required level of humidity, and ambient humidity indicator.
2 speeds and 3 operating modes: MANUAL, CONTINUOUS & AUTOMATIC.
Automatic mode will select the level of humidity based on the ambient temperature.
Programmable 1-24 hour run-on timer.
Anti-frost function: activates when the ambient temperature falls below approximately 15°C.
Automatic reset in the event of a power cut.
Warning sign when the water tank saturates.
Automatic shut-off function: activates when the water tank is full.
Carrying handles.



Control panel.



Wheels.



Easy-clean air filter.



Continuous water drainage device.



Removable water tank.

TECHNICAL CHARACTERISTICS

Model	Voltage 50Hz (V)	Power (W)	Absorbed current (A)	Sound power level (dB(A))	Dehumidification capacity (litres/24H.) [30°C/80 R.H.]	Surface area of influence* (m ²)	Operating temperature	Electronic humidistat	Speeds	Coolant	Colour	Weight (kg)	Dimensions (mm)
DHUM-12 E	230	260	1,2	40	12	30	5 - 32°C	•	2	R134A	White RAL 9003 / Black RAL 9005	11,2	365x220x490
DHUM-20 E	230	480	2,1	42	20	45	5 - 32°C	•	2	R134A	White RAL 9003 / Black RAL 9005	13,7	365x220x490
DHUM-30 E	230	650	3	46	30	50	5 - 32°C	•	2	R410A	White RAL 9003 / Black RAL 9005	18,5	481x286x628

* Information provided as guidance for ceiling heights of 2.5 m.