



Technologies

- Solid lock body made from brass
- Hardened steel shackle with NANO PROTECT™ plating for extreme corrosion resistance
- Inner components made from non-corrosive materials
- Precision pin tumbler cylinder
- Shackles available in different lengths (HB)
- 65CS: shackle guard protects shackle from attack

Operation and use

- 65MB/15 - 65/25: To secure valuables / goods of lesser value or at a low risk of theft
- 65/30 - 60: To secure valuables / goods of medium value or at an average risk of theft
- 15 - 25 mm: To secure bags, suitcases, jewellery boxes, cash boxes, etc.
- 30 - 60 mm: To secure chains, doors, gates, cupboards, lockers, tool boxes, cellar windows, sheds, switchboards, etc.

Variants

- Sizes: 15, 20, 25, 30, 35, 40, 45, 50, 60 mm
 - Long shackle (HB): 30HB60, 40HB40, 40HB63, 50HB80
 - Stainless steel shackle (IB): 40
-

Technical data - 65MB/15

Depth e	10 mm
Height f	40 mm
Horizontal clearance b	8 mm
Keyed alike	No
Locking type	key
Security Level Home Security	3
Security card	No
Shackle diameter d	3 mm
Vertical clearance c	20 mm
Weight	25 g
Width a	16 mm
colour	brass
EAN	4003318093258

Technical drawing

