

2180 3

Pipe cutter

for stainless steel pipes

Code	ETIM
2964066	EC000148
EAN	UNSPSC
4017981012485	27-11-15-13
Country of origin	eCl@ss
Spain	21-04-03-02
Customs tariff number	
	82034000



Article description

- Easy cutting due to ball-bearing pressure rollers and cutting wheels
- Cutting wheel changeable without tools
- With retractable deburring tool, spare cutting wheel in handle
- Cutting wheel with high service life
- No. 2180 3 and 2180 4 Body in die-cast magnesium, No. 2180 5 Body in die-cast aluminium
- No. 2180 5 with quick adjustment
- Painted blue

Article information

Contents [Qty of pieces]	1	Wall thickness [max.]	2,5 mm
Net weight [kg]	0,365 kg	Wall thickness [min./max.]	0,7-2,5
Total length [mm]	160 mm	Pipe diameter (max.) [mm]	35 mm
Total width [mm]	65 mm	Pipe diameter (min./max.) [inch]	-
Total height [mm]	40 mm	Pipe diameter (min./max.) [mm]	3-35
Pipe diameter (min.) [mm]	3 mm	Quick adjustment	no
Wall thickness (min.)	7,0 mm		