

Mini-Lynx Fast Start Spiro

ML SPIRAL 827 B22 20W SLV

0035205

Range features



CE

PRODUCT OVERVIEW

Ordering number	0035205
Technology	Compact Fluorescent
Light colour	827 Homelight
Energy class	A
Average life (Rated) (h)	10000
Lamp shape	Spiral
Lamp finish	Frosted
Dimmable	No
Cap/Base	B22
Type	SPIRAL
EAN code	5410288352053
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	1250
Efficacy (Rated) (lm/w)	63
Watt (Nominal) (W)	20
Equivalent watt (W)	90
Voltage (V)	220-240

Mini-Lynx Fast Start Spiro

ML SPIRAL 827 B22 20W SLV

0035205

DATA TABLE

General data

Ordering number	0035205
Dry applications use only	Yes
Technology	Compact Fluorescent
Energy saving lamp	Yes
Energy class	A
Average life (Rated) (h)	10000
Average life (Nominal) (h)	10000
Lamp finish	Frosted
Lamp shape	Spiral
Dimmable	No
Cap/Base	B22
Type	SPIRAL
EAN code	5410288352053
E-number SE	8357564
Long description	
Product name	ML SPIRAL 827 B22 20W SLV
Lamp mercury content (mg)	<2
Starting time (max) (s)	<1.0
Warm-up time to 60% of full light (max) (s)	<40
Control gear required	NO
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	30000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25

Optical data

Light colour	827 Homelight
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	1250
Lumen maintenance at end of nominal life (%)	65
Luminous flux (Nominal) (lm)	1250

Mini-Lynx Fast Start Spiro

ML SPIRAL 827 B22 20W SLV

0035205

Electrical data

kWh per 1000 hours burning time	20
Efficacy (Rated) (lm/w)	63
Watt (Rated) (W)	20
Watt (Nominal) (W)	20
Equivalent watt (W)	90
Voltage (V)	220-240
Lamp power factor	=0.55

Physical data


Weight (kg)	0.07
Lamp Length (mm) - C/L	108±3
Max. Lamp Diameter (mm) - D	55±1
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	12.00 x 6.00 x 6.00
Outer package dimensions (L x W x H) (cm)	31.00 x 13.00 x 15.00

Mini-Lynx Fast Start Spiro

ML SPIRAL 827 B22 20W SLV

0035205

TECHNICAL DRAWINGS



ENERGY LABEL

