



Part Number : 1300700020
Product Description : BradPower D-Size (1 3/8"-M35) Locking Clip, 44.96mm Diameter
Series Number : 130070
Status : Active
Product Category : Industrial Accessories
Engineering Number : 66200A-10



Documents & Resources

Drawings
[1300700020_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Industrial Accessories
Series	130070
Description	BradPower D-Size (1 3/8"-M35) Locking Clip, 44.96mm Diameter
IP Rating	N/A
Product Name	BradPower D-Size
Type	Accessory - Locking Clip
UPC	78678882759

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	N/A

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Keyway	N/A
Material - Connector Body	Polyester
Material - Contact	N/A
Material - Coupling Nut	N/A
Material - Plating Mating	n/a
Net Weight	127.721/g
Poles	N/A
Temperature Range - Operating	-20°C to +90°C
Wire Size (AWG)	N/A
