



PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 10:37 (UTC)

MOTION & CONTROL
NSK



23032CDE4

Spherical Roller Bearings

Boundary Dimensions


d	160	mm	Bore diameter
D	240	mm	Outside diameter
B	60	mm	Width
r (min.)	2.1	mm	Chamfer dimension

Basic Load Ratings

Cr	675000	N	Basic dynamic load rating
C0r	955000	N	Basic static load rating

Speeds

Thermal Speed Rating (Oil-bath)	2400	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	3200	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	1300	min-1	Grease lubrication
Oil (Oil-bath)	1700	min-1	Oil-bath lubrication



Abutment and Fillet Dimensions

da (min.)	172	mm	Diameter of shaft abutment
da (max.)	179	mm	Diameter of shaft abutment
Da (min.)	216	mm	Diameter of housing abutment
Da (max.)	228	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

Calculation factors

e	0.22	Constant
Y2	4.5	Axial load Factors
Y3	3	Axial load Factors
Y0	2.9	Axial load Factors

Mass

Mass approx.	9.66	kg	Mass approx.
--------------	------	----	--------------

