

TM171AETH

Modicon M171 Performance Plug-in Ethernet Modbus TCP

Local Stock Code: Not on Stock



Main

Range of product	Modicon M171
Product or component type	Communication module
Communication port protocol	HTTP Ethernet SMTP BACnet IP Modbus TCP

Complementary

Integrated connection type	Ethernet RJ45 - twisted pair
Physical interface	RJ45 - 100BASE-TX
Supply	Via base board EVD/EVC
Product compatibility	Logic controller M171 performance
Product weight	0.077 Kg

Environment

Product certifications	cURus[RETURN]EAC[RETURN]CSA[RETURN]CE
Marking	CE
IP degree of protection	IP20
Ambient air temperature for operation	-10...55 °C
Ambient air temperature for storage	-20...85 °C
Relative humidity	10...90 % without condensation

Ordering and shipping details

Category	US1PC1222537
Discount Schedule	PC12
GTIN	3606480752506
Returnability	Yes
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.0 Cm
Package 1 Width	9.1 Cm
Package 1 Length	18.5 Cm
Package 1 Weight	176.0 G
Unit Type of Package 2	S02
Number of Units in Package 2	6
Package 2 Height	15.0 Cm
Package 2 Width	30.0 Cm
Package 2 Length	40.0 Cm
Package 2 Weight	1.357 Kg

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is k
Mercury free	Yes
Sustainable packaging	Yes
Packaging made with recycled cardboard	Yes
REACH Regulation	Reference contains Substances of Very High Concern above the threshold 
EU RoHS Directive	Compliant By Exemption 
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and neve

Contractual warranty

Warranty (in months)	18
----------------------	----

Product Life Status : **Commercialised**