

FEATURES

- Portable fan heater
- Dimensions of 645 mm (H) x 565 mm (W) x 860 mm (D)
- Maximum output power of 30 kW
- Operating frequency of 50 Hz
- Three power settings
- On / off switch
- Thermostat controls
- 415 V plug
- Noise level of 61 dB(A)
- Air flow of 1900 m³/h
- Average current of 43.3 A

30kW Fan Heater, Portable, 415 V BS4343/IEC60309

RS Stock No.: 839-5280



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Adjust the temperature of your space with this portable 30 kW fan heater, which offers both heating and cooling functions. It's fitted with integrated thermostat controls for consistent warmth. As part of the RS PRO range, this product has been tested to ensure it delivers high-quality and performance. Safe and reliable, this handy fan heater has safety features such as overheating protection and a thermally protected fan motor. The motor switches itself off when excess heat is generated within the circuitry. As it's possible to use the fan without the heating function, it can also be used to cool rooms.

General Specifications

Heat Type	Fan
Air Flow	1900m ³ /h
Control Type	Thermostat, On/Off Switch
Power Settings	3
Applications	Automobile workshop, Construction area, Assembly operation, Food and beverage, Storeroom and workshop, Greenhouse

Electrical Specifications

Maximum Output Power	30kW
Voltage Rating	400Vac
Nominal Current	43.3A
Frequency	50Hz
Plug Type	415 V BS4343/IEC60309
Noise Level	61dB(A)

Mechanical Specifications

Mounting	Portable
Dimensions	645mm x 565mm x 860mm
Height	645mm
Width	565mm
Depth	860mm
Weight	32.5kg

Approvals

Compliance/Certifications	EN61340
----------------------------------	---------







	839-5283	839-5286	839-5280
Max. Airflow rate	980 m ³ /hour	1100 m ³ /hour	1900 m ³ /hour
Heating Capacity	4.5 / 9 kW	5 / 10 / 15 kW	15 / 30 kW
Current Consumption	13 A	21.7 A	43.3 A
Input Voltage	400 V / 50 Hz	400 V / 50 Hz	400 V / 50 Hz
Sound Level	55 dB	57 dB	61 dB
Dimensions	340 / 335 / 410 mm	395 / 380 / 445 mm	860 / 565 / 645 mm
Weight	10.8 kg	19 kg	32.5 kg