

MFM SERIES - MICRONIC FILTER

MFMC - Replacement cartridge for MFM regular - Coalescing filter : 1 µm



Part number	Flow rate at 7 bar (m3/h) (ΔP= 0,08 bar)	Temperature min/max (°C)	Max. operating pressure (bar)	Filtration (µm)
MFMC 5532	55	3 / 80	20	1
MFMC 7040	70	3 / 80	20	1
MFMC 10060	100	3 / 80	20	1
MFMC 15090	150	3 / 80	20	1
MFMC 225130	225	3 / 80	20	1
MFMC 300175	300	3 / 80	20	1
MFMC 400235	400	3 / 80	20	1
MFMC 500295	500	3 / 80	20	1
MFMC 800470	800	3 / 80	20	1
MFMC 1550910	1.550	3 / 80	20	1