

KAXZ1S142

Cam switch operating head, Harmony K,
22mm, metal, circular 29mm, key operated 45
degree, Ronis 421

Main

Range of product	Harmony Series K
Product or component type	Cam switch operating head
Component name	KAX
Product compatibility	Front mounting bodies 12 and 20 A by Ø 22 mm hole
Cam switch head type	With bezel Ø 28.5 mm, metal
Type of operator	Key key 421
Rotary handle padlocking	Without
Presentation of legend	With mat black legend
Switching angle	45 °

Complementary

Mechanical durability	1000000 cycles
Net weight	0.065 kg
Compatibility code	KAX

Environment

Protective treatment	TC
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...70 °C
Shock resistance	30 gn conforming to IEC 68-2-27
Vibration resistance	5 gn conforming to IEC 68-2-6 (f = 10...150 Hz)
IP degree of protection	IP65 conforming to IEC 529 IP65 conforming to NF C 20-010

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration